

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

1200 Grooves, 12.5 X 25mm, 500nm Ruled Diffraction Grating



Reflective Ruled Diffraction Gratings

Stock #43-004 3-4 DAYS



1



€105,00

ADD TO CART

Qty 1+

€105,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
1200

Blaze Wavelength (nm):
500

Blaze Angle (°):
17.45

Dimensions (mm):
12.5 x 25.0 ±0.5

Clear Aperture (%) : 90
Coating: Bare Aluminum
Construction: Ruled Grating
Direction of Grooves: Parallel to Short Dimension
Length (mm): 25.00
Substrate: ☐ Float Glass
Thickness (mm): 9.50 ±0.5
Type: Reflective Diffraction Grating
Width (mm): 12.50
Alignment of Grooves to Edge (°): ±0.5
Absolute Peak Efficiency, Typical (%) : 85
Peak Efficiency Avg, Typical (%) : >74

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
