


In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #17-314 CLEARANCE 3-4 DAYS



1



€325,00

ADD TO CART

Qty 1-5

€325,00

Qty 6+

€260,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
12.50 x 12.50

Effective Focal Length EFL (mm):
37.50 @ 587.6nm

Numerical Aperture NA:
0.17

Back Focal Length BFL (mm): 31.09
Substrate:  N-BK7
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: Uncoated
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 11.50 x 11.50
Edge Thickness ET (mm): 8.70
Center Thickness CT (mm): 9.72 ±0.10
f/#: 3.00
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 350 - 2200
Conjugate Distance: Infinite
Power (diopters): 26.67

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View