




12.5 x 12.5mm, 0.20 Numerical Aperture, Uncoated, Square Precision Aspheric Lens



Stock **#17-316** CLEARANCE 3-4 DAYS

⊖ 1 ⊕

€325,00

ADD TO CART

Qty 1-5

€325,00

Qty 6+

€260,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
12.50 x 12.50

Effective Focal Length EFL (mm):

31.25 @ 587.6nm
Numerical Aperture NA: 0.20
Back Focal Length BFL (mm): 23.67
Substrate: ☐ N-BK7
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: Uncoated
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 11.50 x 11.50
Edge Thickness ET (mm): 10.27
Center Thickness CT (mm): 11.50 ±0.10
f/#: 2.50
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 350 - 2200
Conjugate Distance: Infinite
Power (diopters): 32.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View