

12.5 x 12.5mm, 75R/25T, AR Coated Plate Beamsplitter



Stock #13-401 3-4 DAYS

⊖ 1 ⊕ **€47,00**

ADD TO CART

Qty 1-9
€47,00
Qty 10+
€33,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating Specification:
Surface 1: Dielectric, ±5% R/T @ 550nm
Surface 2: AR $\lambda/10$ MgF2 @ 550nm

Construction:
Plate

Dimensional Tolerance (mm):
±0.38

Dimensions (mm): 12.50 x 12.50
Edges: Cut
Reflection/Transmission Ratio (R/T): 75/25
Substrate: ☐ Float Glass
Surface Flatness (P-V): 4 - 6λ
Surface Quality: 80-50
Thickness (mm): 1.00
Type: AR Coated Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant