

TECHSPEC® 12.5 x 12.5mm Protected Gold, 4-6λ Mirror



Stock **#43-791** ☐ In Stock

1 **€38,00**

ADD TO CART

Qty 1-5
€38,00
Qty 6+
€30,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
60-40

Dimensions (mm):

12.5 x 12.5
Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Clear Aperture CA (mm): 11.50 x 11.50
Edges: Seamed, 0.5mm Maximum Edge Chip
Thickness (mm): 2.00
Type: Flat Mirror
Wavelength Range (nm): 700 - 10000
Length (mm): 12.50
Width (mm): 12.50
Damage Threshold, By Design: ☐ 0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant