

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #17-024 3-4 DAYS



1



€1.140,00

ADD TO CART

Qty 1+

€1.140,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Focal Length FL (mm):
125.00

Model Number:
601926

Maximum Diameter (mm):
119.8 +0/-0.2

Scan Angle (°):
37.2

Scan Field (mm):

57 x 57
Mounting Threads: M85 x 1
Telecentricity (°): F-Theta Only: 4.9 With Scanner: 5.1
Type: JENar F-Theta
Weight (g): 860
Working Distance (mm): 154.6
Note: + VS options provide >85% Transmission from 500-680nm
Wavelength Range (nm): 500 - 680, 1030 - 1080
Protective Window: #17-697 : One Included
Manufacturer: Jenoptik
Scan Field Diameter (mm): 80
Flange Distance (mm): 196.9
Focus Size Diameter, 1/e² (µm): 16
GDD Specification (fs²): 3670
Input Beam Diameter, 1/e² (mm): 15
Maximum Length (mm): 58.3

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View