

12.5mm Dia., 1.1mm Thick, Uncoated, SCHOTT Xensation® Chemically Strengthened Window

See More by [SCHOTT Optical Components](#)



Stock #17-260 3-4 DAYS

⊖ 1 ⊕ **€19,00**

ADD TO CART

Qty 1-5
€19,00

Qty 6+
€15,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Bevel:
Protective as needed

Clear Aperture (%):
90

Clear Aperture CA (mm): 11.25
Diameter (mm): 12.50 ±0.127
Thickness (mm): 1.10 Nominal
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 8.8 (+20 to +300°C)
Density (g/cm³): 2.48
Edges: Fine Ground
Index of Refraction n_d: 1.51
Knoop Hardness (kg/mm²): 639
Poisson's Ratio: 0.215
Substrate: SCHOTT Xensation®
Surface Quality: 80-50
Transformation Temperature (°C): 615
Type: Protective Window
Wavelength Range (nm): 380 - 840
Young's Modulus (GPa): 74

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant