

**TECHSPEC® 12.5mm Dia., 1mm Thick, BBAR (1650-3000nm) AR Coated Sapphire Window**



Stock **#15-991** 3-4 DAYS

⊖ 1 ⊕ **€83,00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-24                      |
| €83,00                        |
| Qty 25+                       |
| €66,50                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Abbe Number (v<sub>d</sub>):**  
72.24

**Axis Orientation:**  
Random

**Bevel:**  
Protective as needed

|                                                                                                                |
|----------------------------------------------------------------------------------------------------------------|
| <b>Birefringence (<math>n_o - n_e</math>):</b><br>0.008 for Visible Light Orthogonal to Optical Axis           |
| <b>Clear Aperture (%)</b> :<br>≥90                                                                             |
| <b>Clear Aperture CA (mm)</b> :<br>11.25                                                                       |
| <b>Diameter (mm)</b> :<br>12.50 ±0.15                                                                          |
| <b>Thickness (mm)</b> :<br>1.00 ±0.05                                                                          |
| <b>Coating</b> :<br>BBAR (1650-3000nm)                                                                         |
| <b>Coating Specification</b> :<br>R <sub>avg</sub> <1% @ 1650 - 3000nm<br>R <sub>abs</sub> <2% @ 1650 - 3000nm |
| <b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C)</b> :<br>8.8                                      |
| <b>Density (g/cm³)</b> :<br>3.97                                                                               |
| <b>Edges</b> :<br>Fine Ground                                                                                  |
| <b>Index of Refraction <math>n_d</math></b> :<br>1.77                                                          |
| <b>Knoop Hardness (kg/mm²)</b> :<br>1900                                                                       |
| <b>Parallelism (arcmin)</b> :<br>≤3.5                                                                          |
| <b>Poisson's Ratio</b> :<br>0.27                                                                               |
| <b>Substrate</b> :<br>Sapphire (Al <sub>2</sub> O <sub>3</sub> )                                               |
| <b>Surface Flatness (P-V)</b> :<br>2λ (typical)                                                                |
| <b>Surface Quality</b> :<br>80-50                                                                              |
| <b>Type</b> :<br>Protective Window                                                                             |
| <b>Wavelength Range (nm)</b> :<br>1650 - 3000                                                                  |
| <b>Young's Modulus (GPa)</b> :<br>435                                                                          |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |