

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

12.5mm Square, Red Dichroic Filter



Additive and Subtractive Dichroic Color Filters

Stock #11-484 In Stock



1



€22,00

ADD TO CART

Qty 1-24

€22,00

Qty 25+

€19,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
12.5 x 12.5

Angle of Incidence (°):
0

Cut-On Wavelength (nm):
605.00

Substrate: 

Length (mm):
12.50

Operating Temperature (°C):
<100

Coating:
Additive Color

Color:
Red

Surface Quality:
80-50

Thickness (mm):
2.00 Nominal

Type:
Dichroic Filter

Width (mm):
12.50

Dimensional Tolerance (mm):
±0.25

Clear Aperture (%):
≥85

Cut-On Wavelength Tolerance (µm):
0.012

Coating Specification:
T_{avg} <1.0% @ 390 - 570nm, T_{avg} >85% @ 620 - 750nm
T_{abs} <2.0% @ 415 - 550nm, T_{abs} >80% @ 630 - 750nm

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)