

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union




SUBMIT

TECHSPEC® 12.5mm Dia. 400 - 750nm Broadband $\lambda/10$ Mirror



TECHSPEC Broadband Dielectric $\lambda/10$ Mirrors



Stock #87-368 □ In Stock



1



€75,00

ADD TO CART

Qty 1-5

€75,00

Qty 6+

€60,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
Dielectric Mirror (400-750nm)

Coating Specification:

R_{avg} >98% @ 400 - 750nm (0 - 45°) R_{avg} >99% @ 400 - 750nm (0°)
Wavelength Range (nm): 400 - 750
Diameter (mm): 12.50 +0.00/-0.20
Surface Flatness (P-V): λ/10
Substrate: Fused Silica (Corning 7980)
Back Surface: Commercial Polish
Surface Quality: 20-10
Coating Type: Dielectric
Angle of Incidence (°): 0-45
Clear Aperture (%): 90
Edges: Ground, 0.5mm max bevel
Parallelism (arcmin): <0.5
Thickness (mm): 3.00 ±0.20
Type: Flat Mirror
Damage Threshold, Reference: 0.5 J/cm² @ 532nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View