

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 12.5mm Dia. x 20mm FL, MgF₂ Coated, Achromatic Doublet Lens



MgF₂ Coated Achromatic Lenses



Stock #32-309 ☒ In Stock

☐ [Other Coating Options](#)

1

€76,00

ADD TO CART

Qty 1-5

€76,00

Qty 6+

€60,75

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.025

Effective Focal Length EFL (mm): 20.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 16.45
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 11.50
Centering (arcmin): <1
Center Thickness CT (mm): 6.35 ±0.10
Center Thickness CT 1 (mm): 5.25 ±0.05
Center Thickness CT 2 (mm): 1.10 ±0.05
Radius R₁ (mm): 13.98
Radius R₂ (mm): -9.35
Radius R₃ (mm): -76.14
Edge Thickness ET (mm): 4.62
Substrate: S-BAH11 / N-SF10
Surface Quality: 40-20
f/#: 1.6
Numerical Aperture NA: 0.31
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View