

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

12.5mm Square, Green Dichroic Filter



Additive and Subtractive Dichroic Color Filters

Stock #11-483 3-4 DAYS

1

€22,00

ADD TO CART

Qty 1-24

€22,00

Qty 25+

€19,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
12.5 x 12.5

Angle of Incidence (°):
0

Cut-Off Wavelength (nm):
575.00

Cut-On Wavelength (nm): 505.00
Substrate: 
Length (mm): 12.50
Operating Temperature (°C): <100
Coating: Additive Color
Color: Green
Surface Quality: 80-50
Thickness (mm): 2.00 Nominal
Type: Dichroic Filter
Width (mm): 12.50
Dimensional Tolerance (mm): ±0.25
Clear Aperture (%): ≥85
Cut-On Wavelength Tolerance (µm): 0.012
Coating Specification: T _{avg} <1.0% @ 400 - 480nm, T _{avg} >80% @ 525 - 555nm, T _{avg} <1.0% @ 590 - 720nm T _{abs} <1.0% @ 425 - 455nm, T _{abs} >70% @ 530 - 550nm, T _{abs} <1.0% @ 620 - 690nm
Cut-Off Wavelength Tolerance (µm): 0.012

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant