


TECHSPEC® 12.7 x 12.7mm 343nm 0-45°, Yb:YAG Laser Line Mirror



TECHSPEC® Yb:YAG Laser Line Mirrors

Stock **#39-604** 3-4 DAYS

⊖ 1 ⊕ **€150,00**

ADD TO CART

Qty 1-5

€150,00

Qty 6+

€135,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%) 85
Back Surface: Commercial Polish
Reflection at DWL (%) 99.8
Coating Specification: R_{abs} >99.8% @ 343nm
Wavelength Range (nm): 339 - 346
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (343nm)
Design Wavelength DWL (nm): 343
Dimensions (mm): 12.7 x 12.7 +0.00/-0.10
Thickness (mm): 6.35 ±0.20
Angle of Incidence (°): 0-45
Substrate: ☐ Fused Silica (Corning 7980)
Damage Threshold, By Design: ☐ 5 J/cm² @ 343nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View