

TECHSPEC® 12.5mm Dia. 1064nm 0-45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors



Stock **#88-532** 3-4 DAYS

⊖ 1 ⊕

€144,00

ADD TO CART

Qty 1-5

€144,00

Qty 6+

€127,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mrror

Parallelism (arcmin): <3
Clear Aperture (%): >90
Back Surface: Ground
Reflection at DWL (%): 99.9
Coating Specification: R _{abs} >99.8% @ 1064nm
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (1064nm)
Design Wavelength DWL (nm): 1064
Diameter (mm): 12.50 +0.0/-0.2
Thickness (mm): 6.00 ±0.2
Angle of Incidence (°): 0-45
Substrate: ☐ Fused Silica (Corning 7980)
Damage Threshold, Reference: ☐ 15 J/cm² @ 1064nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View