

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 12.5mm Dia. 266nm 45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock #47-980 3-4 DAYS



1



€120,00

ADD TO CART

Qty 1-5

€120,00

Qty 6+

€105,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%) >90
Back Surface: Ground
Reflection at DWL (%) 99.5
Coating Specification: R_{abs} >99.5% @ 266nm @ 45° AOI R_{avg} >99.5% @ 263 - 268nm @ 45° AOI
Wavelength Range (nm) 263 - 268
Surface Flatness (P-V): $\lambda/10$
Coating Type: Dielectric
Coating: Laser Mirror (266nm)
Design Wavelength DWL (nm) 266
Diameter (mm) 12.50 +0.0/-0.2
Thickness (mm) 6.00 ±0.2
Angle of Incidence (°) 45
Substrate: Fused Silica (Corning 7980)
Damage Threshold, Reference: 2.5 J/cm² @ 266nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View