


12.7mm 5°, 2µm Highly-Dispersive Broadband Ultrafast Mirror

See More by [UltraFast Innovations \(UFI\)](#)



Stock #11-413 3-4 DAYS

⊖ 1 ⊕ **€683,00**

ADD TO CART

Qty 1-3

€683,00

Qty 4+

€602,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:
Laser Mirror

Typical Applications:
Thulium and Holmium Lasers

Wedge (arcmin):
10

Clear Aperture (%): 80
Back Surface: Commercial Polish
Reflection at DWL (%): >99.95
Reflectivity (Rp%): 99.9
Coating Specification: Ravg >99.9% @ 2000 - 2200nm (p-polarization)
GDD Specification: -1000fs² @ 2000 - 2200nm (p-polarization)
Wavelength Range (nm): 2000 - 2200
Irregularity (P-V) @ 632.8nm: λ/10
Coating Type: Dielectric
Coating: Chirped Ultrafast (2000-2200nm)
Design Wavelength DWL (nm): 2000
Diameter (mm): 12.70 +0.0/-0.1
Thickness (mm): 6.35 ±0.01
Angle of Incidence (°): 5
Substrate: ☐ Fused Silica (Corning 7980)

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant