

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

12.7mm 7°, 1030nm Highly-Dispersive Ultrarast Mirror

See More by [UltraFast Innovations \(UFI\)](#)



Stock #12-334 3-4 DAYS



1



€458,00

ADD TO CART

Qty 1-3

€458,00

Qty 4+

€400,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Design Wavelength DWL (nm):
1030

Wavelength Range (nm):
1010 - 1070

Diameter (mm):
12.70 +0.0/-0.1

Angle of Incidence (°): 7
Reflection at DWL (%): 99.9 (typical, s-polarization)
Thickness (mm): 6.35 ±0.2
Substrate: Fused Silica (Coming 7980)
Type: Laser Mirror
Coating Type: Dielectric
Coating Specification: R_{avg} >99.8%, GDD = -1000fs² @ 1010 - 1070nm (s-polarization) R_{abs} >99.9% @ 1030nm (typical, s-polarization)
GDD Specification: -1000fs² @ 1010 - 1070nm
Back Surface: Commercial Polish
Clear Aperture (%): 80
Coating: Ultrafast (1010-1070nm)
Typical Applications: Yb:doped 1st Harmonic
Irregularity (P-V) @ 632.8nm: λ/10
Wedge (arcmin): 10 ±5
Minimum Reflectivity : >99.8% @ 1010 - 1070nm (s-polarization)
Damage Threshold, By Design: 0.3 J/cm² @ 1030nm, 50fs, 1kHz, 100μm Beam Diameter

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant