

12.7mm Dia., 650 - 1350nm, Complementary Chirped Mirror Pair

See More by [UltraFast Innovations \(UFI\)](#)



UltraFast Innovations (UFI) Ultra-Broadband Complementary Chirped Mirror Pairs

Stock #14-673 3-4 DAYS

- 1 + **€1.406,00**

ADD TO CART

Qty 1-9
€1.406,00

Qty 10+
€1.241,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Wedge (arcmin):
10 ±5

Clear Aperture (%):
80

Back Surface:

Commercial Polish
Coating Specification: R _{avg} >99% @ 650 - 1350nm (3° AOI, p-polarization)
GDD Specification: -60fs ² @ 650 - 1350nm (3° AOI, p-polarization)
Wavelength Range (nm): 650 - 1350
Irregularity (P-V) @ 632.8nm: λ/10
Coating Type: Dielectric
Coating: Complementary Chirped Pair (650-1350nm)
Diameter (mm): 12.70 +0.00/-0.10
Thickness (mm): 6.35 ±0.20
Angle of Incidence (°): 5
Substrate: ☐ Fused Silica (Corning 7980)
Note: Sold as a Set of 2
Damage Threshold, By Design: ☐ 0.2 J/cm ² @ 800nm, 50fs
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant