


In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 12.7 X 12.7 mm 343nm 45°, Yb:YAG Laser Line Mirror



TECHSPEC® Yb:YAG Laser Line Mirrors

Stock #39-596 3-4 DAYS



1



€137,00

ADD TO CART

Qty 1-5

€137,00

Qty 6+

€123,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%): 85
Back Surface: Commercial Polish
Reflection at DWL (%): 99.8
Coating Specification: R_{abs} >99.8% @ 343nm R_{avg} >99.5% @ 339 - 346nm
Wavelength Range (nm): 339 - 346
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (339-346nm)
Design Wavelength DWL (nm): 343
Dimensions (mm): 12.7 x 12.7 +0.00/-0.10
Thickness (mm): 6.35 ±0.20
Angle of Incidence (°): 45
Substrate: □ Fused Silica (Corning 7980)
Damage Threshold, Reference: □ 6 J/cm² @ 343nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View