


In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 12.7 X 12.7 mm Laser Mirror Substrate



TECHSPEC® Laser Mirror Substrates

Stock #37-724 3-4 DAYS



1



€98,00

ADD TO CART

Qty 1-10

€98,00

Qty 11+

€88,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror Substrate

Parallelism (arcmin):
<3

Clear Aperture (%) : 85
Back Surface : Commercial Polish
Surface Flatness (P-V) : λ/10
Coating : Uncoated
Dimensions (mm) : 12.7 x 12.7 +0.00/-0.10
Thickness (mm) : 6.35 ±0.20
Substrate : Fused Silica (Corning 7980)

Regulatory Compliance

RoHS 2015 : Compliant
Reach 209 : Compliant
Certificate of Conformance : View