


TECHSPEC® 12.7 x 12.7mm x 50mm FL, Uncoated Imaging Grade PCX Cylinder Lens



Stock **#34-752** ☐ In Stock

1 **€89,00**

ADD TO CART

Qty 1-5
€89,00
Qty 6+
€71,00
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
50.00

Substrate: ☐
[N-BK7](#)

f/#: 8.00
Numerical Aperture NA: 0.13
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 48.68
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.00
Center Thickness Tolerance (mm): ±0.1
Clear Aperture CA (mm): 11.43 x 11.43
Dimensional Tolerance (mm): +0.0/-0.025
Dimensions (mm): 12.7 x 12.7
Edge Thickness ET (mm): 1.21
Radius R₁ (mm): 25.84
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Plano Axis Wedge (arcmin): <5
Power Axis Wedge (arcmin): <5
Axial Twist (arcmin): <3

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View