

TECHSPEC® 12.7mm Dia. x 200mm FL, 1064nm Coated, Laser Grade PCX Lens



TECHSPEC Laser Grade PCX Lenses

Stock **#38-739** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕ **€183,00**

ADD TO CART

Qty 1-5

€183,00

Qty 6+

€146,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.70 +0.00/-0.025

Effective Focal Length EFL (mm):
200.00 @ 355nm

Back Focal Length BFL (mm):

197.35
Coating: Laser V-Coat (1064nm)
Coating Specification: R _{abs} <0.25% @ 1064nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 10-5
Power (P-V) @ 632.8nm: λ
Irregularity (P-V) @ 632.8nm: λ/10
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 4.00 ±0.10
Edge Thickness ET (mm): 3.79
Radius R₁ (mm): 95.22
Clear Aperture CA (mm): 11.43
f/#: 15.75
Numerical Aperture NA: 0.03
Design Wavelength DWL (nm): 1064
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Damage Threshold, By Design: ☐ 15 J/cm² @ 1064nm, 20ns, 20Hz

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View