

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Lithium Fluoride (LiF) Windows

Stock #16-804 3-4 DAYS



1



€285,00

ADD TO CART

Qty 1-10

€285,00

Qty 11+

€256,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number (v_d):
97.29

Axis Orientation:
Random

Bevel:

Protective as needed
Clear Aperture (%) : 85
Clear Aperture CA (mm) : 10.80
Diameter (mm) : 12.70 +0.00/-0.13
Thickness (mm) : 1.00 ±0.13
Coating : Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C) : 37
Density (g/cm³) : 2.64
Edges : Fine Ground
Index of Refraction n_d : 1.392 @ 0.6µm
Knoop Hardness (kg/mm²) : 102
Parallelism (arcmin) : <3
Poisson's Ratio : 0.33
Substrate : Lithium Fluoride (LiF)
Surface Flatness (P-V) : 2λ @ 632.8nm
Surface Quality : 60-40
Type : Protective Window
Wavelength Range (nm) : 150 - 6000
Young's Modulus (GPa) : 64.97

Regulatory Compliance

RoHS : Compliant
Certificate of Conformance : View