

TECHSPEC® 12.7mm Dia. x 50.8mm FL, 8-12µm BBAR Coated, ZnSe Plano-Convex Lens

See More by [Coherent®](#)



TECHSPEC Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses

Stock **#39-546** 3-4 DAYS

[Other Coating Options](#)

- 1 + **€285,00**

ADD TO CART

Qty 1-10
€285,00
Qty 11+
€256,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.70 +0.00/-0.10

Effective Focal Length EFL (mm):
50.80 @ 10.6µm

Back Focal Length BFL (mm): 49.97
Coating: BBAR (8000-12000nm)
Coating Specification: R _{avg} ≤0.5% @ 8 - 12μm
Substrate: ☐ Coherent® Infrared ZnSe
Surface Quality: 40-20
Power (P-V) @ 632.8nm: λ
Power (P-V) @ 10.6μm: λ10
Irregularity (P-V) @ 10.6μm: λ20
Centering, ETD (μm): ≤50.8
Center Thickness CT (mm): 2.00 ±0.10
Edge Thickness ET (mm): 1.72
Radius R₁ (mm): 71.26
Clear Aperture CA (mm): 11.43
f/#: 4.00
Numerical Aperture NA: 0.13
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 8000 - 12000
Bulk Absorption Coefficient (cm⁻¹): <0.0005 @ 10.6μm
Surface Roughness (Angstroms): <50 RMS

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View