

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 12.7 mm Dia., 715 - 980nm, 90R:10T, Ultrarast Beamsplitter



TECHSPEC® Ultrarast Beamsplitters

Stock #13-829 3-4 DAYS



1



€222,00

ADD TO CART

Qty 1-4

€222,00

Qty 5+

€197,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):
45

Diameter (mm):
12.70 +0.00/-0.10

Substrate: ☐
[Fused Silica](#) (Coming 7980)

Surface Quality: 10-5
Thickness (mm): 3.00 ±0.10
Type: Ultrafast Non-Polarizing Beamsplitter
Clear Aperture (%): 80
Parallelism (arcsec): <10
Reflection/Transmission Ratio (R/T): 90/10
Coating Specification: Surface 1: R _{avg} = 90±3% @ 715 - 980nm R _p = 83±3% @ 715 - 980nm R _s = 97±3% @ 715 - 980nm Surface 2: R _s <2% @ 650 - 1100nm R _p <1.5% @ 650 - 1100nm
Wavelength Range (nm): 715 - 980
GDD Specification: Transmission: ±65 fs ² @ 715 - 980nm Reflectivity: ±75 fs ² @ 715 - 980nm
Transmitted Wavefront Distortion: λ/8 @ 632.8nm
Reflected Wavefront Distortion: <λ/3 @ 632.8nm

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View