


TECHSPEC® 12.7mm Dia. Laser Mirror Substrate



TECHSPEC® Laser Mirror Substrates

Stock **#37-684** 3-4 DAYS

⊖ 1 ⊕ **€77,00**

ADD TO CART

Qty 1-10

€77,00

Qty 11+

€67,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror Substrate

Parallelism (arcmin):
<3

Clear Aperture (%) : 90
Back Surface : Commercial Polish
Surface Flatness (P-V) : λ/10
Coating : Uncoated
Diameter (mm) : 12.70 +0.00/-0.10
Thickness (mm) : 6.35 ±0.20
Substrate : Fused Silica (Corning 7980)

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant