


TECHSPEC® 12.7mm Diameter x 150mm FL, 1900-2200nm Coated, IR Ultrafast Thin PCX Lens



Stock **#11-618** [CONTACT US](#)

[Other Coating Options](#)



1



€110,00

ADD TO CART

Qty 1-5

€110,00

Qty 6+

€98,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.70 +0.00/-0.10

Effective Focal Length EFL (mm):
150.17 @587.6nm

Back Focal Length BFL (mm):

149.15
Coating: BBAR (1900-2200nm)
Coating Specification: R _{abs} <0.15% @ 1900 - 2200nm
Substrate: ☐ Fused Silica IR Grade
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/8
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 1.50 ±0.10
Edge Thickness ET (mm): 1.21
Radius R₁ (mm): 68.85
Clear Aperture CA (mm): 11.43
f/#: 11.82
Numerical Aperture NA: 0.043
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 1900 - 2200
Angle of Incidence (°): 0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View