

12.7mm Diameter x 15mm FL, MgF₂ Coated, PCX Condenser Lens



Stock **#15-529** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕

€39,00

ADD TO CART

Qty 1-10
€39,00
Qty 11+
€35,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.70 +0.1/-0.3

Effective Focal Length EFL (mm):
15.00

Numerical Aperture NA:
0.42

Substrate: Float Glass
Focal Length Tolerance (%): ±7
Coating: MgF₂ (400-700nm)
Coating Specification: R_{avg} ≤ 1.75% @ 400 - 700nm
Centering (arcmin): ≤30
Surface Quality: 80-50 (typical)
Center Thickness CT (mm): 4.40 ±0.2
f/#: 1.18
Bevel: Protective bevel as needed
Radius R₂ (mm): Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 400 - 700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant