

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC® Nd:YAG Laser Line Beam Samplers

Stock #39-008 3-4 DAYS



1



€122,50

ADD TO CART

Qty 1-5

€122,50

Qty 6+

€110,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):
0 ±5

Clear Aperture (%):
90

Coating:
Laser V-Coat (532nm)

Coating Specification: R_{abs} <0.25% @ 532nm
Design Wavelength DWL (nm): 532
Diameter (mm): 12.70 +0.00/-0.10
Index of Refraction n_d: 1.458
Parallelism (arcmin): <3
Substrate: ☐ Fused Silica (Corning 7980)
Surface Flatness (P-V): λ/10
Surface Quality: 10-5
Thickness (mm): 6.35 ±0.20
Type: Beam Sampler
Damage Threshold, By Design: ☐ 10 J/cm² @ 532nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View