

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 12.7 mm Dia. x 300mm FL, Uncoated, Laser Grade PCX Lens



TECHSPEC Laser Grade PCX Lenses

Stock #38-643 3-4 DAYS

[Other Coating Options](#)



1



€145,00

ADD TO CART

Qty 1-5

€145,00

Qty 6+

€116,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.70 +0.00/-0.025

Effective Focal Length EFL (mm):
300.00 @ 355nm

Back Focal Length BFL (mm):

297.38
Coating: Uncoated
Substrate: ☐ Fused Silica (Coming 7980)
Surface Quality: 10-5
Power (P-V) @ 632.8nm: λ
Irregularity (P-V) @ 632.8nm: λ10
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 4.00 ±0.10
Edge Thickness ET (mm): 3.86
Radius R₁ (mm): 142.83
Clear Aperture CA (mm): 11.43
f/#: 23.62
Numerical Aperture NA: 0.02
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 200 - 2200

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View