

TECHSPEC® 12.7mm Dia. x 40.0mm FL, Uncoated, Plano-Convex Lens



Stock **#37-803** 3-4 DAYS
[Other Coating Options](#)

- 1 + **€28,00**

ADD TO CART

Qty 1-9
€28,00
Qty 10+
€25,25
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.70 +0.0/-0.025

Effective Focal Length EFL (mm):

40.00 @ 587.6nm
Back Focal Length BFL (mm): 38.48
Coating: Uncoated
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.30 ±0.10
Edge Thickness ET (mm): 1.30
Radius R ₁ (mm): 20.67
Clear Aperture CA (mm): 11.7
f/#: 3.15
Numerical Aperture NA: 0.16
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View