

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC Laser Grade PCX Lenses

Stock #38-660 3-4 DAYS

[Other Coating Options](#)



1



€183,00

ADD TO CART

Qty 1-5

€183,00

Qty 6+

€146,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.70 +0.00/-0.025

Effective Focal Length EFL (mm):
50.00 @ 355nm

Back Focal Length BFL (mm):

47.30
Coating: Laser V-Coat (266nm)
Coating Specification: R _{abs} <0.25% @ 266nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 10-5
Power (P-V) @ 632.8nm: λ
Irregularity (P-V) @ 632.8nm: λ/10
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 4.00 ±0.10
Edge Thickness ET (mm): 3.14
Radius R₁ (mm): 23.80
Clear Aperture CA (mm): 11.43
f/#: 3.94
Numerical Aperture NA: 0.13
Design Wavelength DWL (nm): 266
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Damage Threshold, By Design: ☐ 3 J/cm ² @ 266nm, 20ns, 20Hz

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View