

TECHSPEC® 12mm Dia. x 100mm FL, NIR I Coated, Plano-Convex Lens



UV Fused Silica Plano-Convex (PCX) Lenses



Stock **#18-060** 3-4 DAYS

- 1 +

€130,00

ADD TO CART

Qty 1-5

€130,00

Qty 6+

€104,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.00 -0.025

Effective Focal Length EFL (mm):

100.00 @587.6nm
Back Focal Length BFL (mm): 98.33
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 3 Rings
Irregularity (P-V) @ 632.8nm: 0.5 Rings
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.44 ±0.05
Edge Thickness ET (mm): 2.05
Radius R₁ (mm): 45.85
Clear Aperture CA (mm): 11
f/#: 8.33
Numerical Aperture NA: 0.06
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 600 - 1050
Damage Threshold, Reference: ☐ 7 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant