

TECHSPEC®

12.7mm Diameter Protected Gold Coated, λ/10 Mirror



Stock #39-193 3-4 DAYS

-

1

+

€95,50

ADD TO CART

Qty 1-5
€95,50

Qty 6+
€76,50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.70 +0.00/-0.10

Surface Flatness (P-V):
λ/10 (measured before coating)

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Back Surface: Commercial Polish
Surface Quality: 20-10
Dimensional Tolerance (mm): +0.0/-0.10
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Edges: Ground
Parallelism (arcsec): <180
Thickness (mm): 6.35 ±0.20
Type: Flat Mirror
Wavelength Range (µm): 0.7 - 10
Wavelength Range (nm): 700 - 10000
Damage Threshold, Reference: ☐ 0.8 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant