

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

12mm Dia. x 12.5mm FL, Uncoated Molded Aspheric Condenser Lens



Molded Aspheric Condenser Lenses

Stock #88-287 3-4 DAYS

[Other Coating Options](#)



1



€31,50

ADD TO CART

|          |
|----------|
| Qty 1-10 |
| €31,50   |

|         |
|---------|
| Qty 11+ |
| €27,90  |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):  
12.00 +/-0.3

Effective Focal Length EFL (mm):  
12.50 @ 587.6nm

Numerical Aperture NA:  
0.48

|                                                                                                                                  |
|----------------------------------------------------------------------------------------------------------------------------------|
| <b>Back Focal Length BFL (mm):</b><br>9.50                                                                                       |
| <b>Substrate:</b> <br><a href="#">Liba2000+</a> |
| <b>Focal Length Tolerance (%):</b><br>±5                                                                                         |
| <b>Coating:</b><br>Uncoated                                                                                                      |
| <b>Centering (arcmin):</b><br>≤30                                                                                                |
| <b>Surface Quality:</b><br>Molded Side: 5/3 x 0.4; E 0.2<br>Polished Side: 5/3 x 0.25; E 0.2                                     |
| <b>Clear Aperture CA (mm):</b><br>9.50                                                                                           |
| <b>Edge Thickness ET (mm):</b><br>1.9                                                                                            |
| <b>Center Thickness CT (mm):</b><br>4.50 ±0.20                                                                                   |
| <b>f#:</b><br>1.04                                                                                                               |
| <b>Bevel:</b><br>Protective bevel as needed                                                                                      |
| <b>Diameter of Asphere (mm):</b><br>12.0                                                                                         |
| <b>Radius R<sub>2</sub> (mm):</b><br>Plano                                                                                       |
| <b>Shape of Back Surface:</b><br>Plano                                                                                           |
| <b>Type:</b><br>Condenser Lens                                                                                                   |
| <b>Wavelength Range (nm):</b><br>350 - 2000                                                                                      |
| <b>Conjugate Distance:</b><br>Infinite                                                                                           |
| <b>Note:</b><br><a href="#">Click here</a> for more information on the ISO 10110 surface quality specification.                  |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |