

TECHSPEC® 12.7mm VIS 0° λ/4 Fresnel Rhomb Retarder



Stock **#36-140** ☐ In Stock

1 **€280,00**

ADD TO CART

Qty 1-5

€280,00

Qty 6+

€260,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):
9.45 x9.45

Coating:
VIS 0° (425-675nm)

Design Wavelength DWL (nm): 532
Substrate: ☐ N-BK7
Retardance: $\lambda/4$
Surface Quality: 20-10
Type: Fresnel Retarder
Dimensional Tolerance (mm): ± 0.10
Bevel: Protective bevel as needed
Coating Specification: $R_{avg} \leq 0.4\%$ @ 425 - 675nm
Wavelength Range (nm): 425 - 675
Width (mm): 12.70
Entrance and Exit Surface (mm): 12.7

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant