

TECHSPEC® 12.7mm Dia., 3.18mm Thick, Fused Silica Uncoated Laser Window Substrate



TECHSPEC® Uncoated Laser Window Substrates

Stock **#37-693** 3-4 DAYS

⊖ 1 ⊕ **€122,50**

ADD TO CART

Qty 1-5

€122,50

Qty 6+

€110,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):
11.43

Coating:
Uncoated

Diameter (mm):
12.70 +0.00/-0.10

Substrate: Fused Silica (Corning 7980)
Index of Refraction n_d: 1.458
Surface Quality: 10-5
Thickness (mm): 3.18 ±0.20
Type: Laser Window Substrate
Parallelism (arcmin): <3
Bevel: Protective as needed
Clear Aperture (%): 90
Abbe Number (v_d): 67.8
Wavelength Range (nm): 200 - 2200
Surface Flatness (P-V): λ/10
Fused Silica Grade: 7980 0F
Edges: Fine Ground
Type of Window: Glass

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View