

# 12.7mm Dia. 532nm $\lambda$ /4 Quartz Waveplate Zero Order



Stock **#85-022** [CONTACT US](#)

- 1 + **€424,00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| €424,00                       |
| Qty 6+                        |
| €342,00                       |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):  
8.00

Coating:  
Laser V-Coat (532nm)

Design Wavelength DWL (nm):  
532

Diameter (mm):

|                                                                                                         |
|---------------------------------------------------------------------------------------------------------|
| 12.70 +0.00/-0.25                                                                                       |
| <b>Substrate:</b> <div>Crystal Quartz</div>                                                             |
| <b>Retardance:</b> <div><math>\lambda/4</math></div>                                                    |
| <b>Surface Quality:</b> <div>10-5</div>                                                                 |
| <b>Thickness (mm):</b> <div>6.40 +0.00/-0.25</div>                                                      |
| <b>Type:</b> <div>Crystalline Waveplate</div>                                                           |
| <b>Construction:</b> <div>Crystalline</div>                                                             |
| <b>Transmitted Wavefront, P-V:</b> <div><math>\lambda/10</math> for central 80% of clear aperture</div> |
| <b>Parallelism (arcsec):</b> <div><math>&lt;3</math></div>                                              |
| <b>Retardance Tolerance:</b> <div><math>\pm \lambda/200</math></div>                                    |
| <b>Temperature Coefficient (<math>\lambda/^{\circ}\text{C}</math>):</b> <div>0.0001</div>               |
| <b>Retardance Order:</b> <div>0</div>                                                                   |

### Regulatory Compliance

|                                                    |
|----------------------------------------------------|
| <b>RoHS 2015:</b> <div>Compliant</div>             |
| <b>Reach 209:</b> <div>Compliant</div>             |
| <b>Certificate of Conformance:</b> <div>View</div> |