

12.7mm Dia. 632.8nm $\lambda/2$ Quartz Waveplate Zero Order



Stock **#85-038** [CONTACT US](#)

- 1 + **€424,00**

ADD TO CART

Qty 1-5
€424,00

Qty 6+
€342,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
8.00

Coating:
Laser V-Coat (632.8nm)

Design Wavelength DWL (nm):
632.8

Diameter (mm):

12.70 +0.00/-0.25
Substrate: Crystal Quartz
Retardance: λ/2
Surface Quality: 10-5
Thickness (mm): 6.40 +0.00/-0.25
Type: Crystalline Waveplate
Construction: Crystalline
Transmitted Wavefront, P-V: λ/10 for central 80% of clear aperture
Parallelism (arcsec): <3
Retardance Tolerance: ±λ/200
Temperature Coefficient (λ/°C): 0.0001
Retardance Order: 0

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View