

TECHSPEC® 12mm Dia. x 12mm FL, Uncoated, Hybrid Asphere



TECHSPEC® Plastic Hybrid Aspheric Lenses

Stock #65-987 CLEARANCE 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕ **€84,00**

ADD TO CART

Qty 1-24

€84,00

Qty 25+

€64,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.00 +0.00/-0.10

Effective Focal Length EFL (mm):
12.00 @ 587.6nm

Numerical Aperture NA:

0.50

Back Focal Length BFL (mm):
9.50

Substrate:
Zeonex E48R

Aspheric Design Wavelength (nm):
587.6

Coating:
Uncoated

Surface Quality:
60-40

Clear Aperture CA (mm):
10.00

Edge Thickness ET (mm):
2.37

Center Thickness CT (mm):
4.30 ±0.10

f#:
1.00

Bevel:
Protective bevel as needed

Operating Temperature (°C):
-30 to +70

Radius R₂ (mm):
48.3

Shape of Back Surface:
Convex

Type:
Aspheric Lens

Wavelength Range (nm):
475 - 675

Conjugate Distance:
Infinite

Regulatory Compliance

Reach 191:
[Compliant](#)

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)
