

Ti:Sapphire Flat Top Beam Shaper 12mm | πShaper 12_12_TiS_HP

See More by [AdlOptica](#)



Stock **#14-279** [CONTACT US](#)

-

1

+

€9.620,00

ADD TO CART

Qty 1-4
€9.620,00

Qty 5+
€8.657,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm): 800
Diameter (mm): 42.00
Entrance Beam Diameter, 1/e² (mm): 12.0 - 12.1

Model Number: πShaper 12_12_TiS_HP
Length (mm): 358.00
Mounting Threads: M27 x 1
Type: Beam Shaper
Weight (g): <530
Wavelength Range (nm): 700 - 900
Style: Flat Top
Damage Threshold, By Design: ☐ 3000 mJ/cm² @ 5ns (typical)
Output Diameter, FWHM (mm): 12.0

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant