

**TECHSPEC® 15.0mm Dia. x 25.0mm FL, VIS 0° Coated, Plano-Convex Lens**



Stock **#38-311** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕ **€41,50**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| €41,50                        |
| Qty 10+                       |
| €37,25                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
15.00 +0.0/-0.025

Effective Focal Length EFL (mm):

|                                                                                       |
|---------------------------------------------------------------------------------------|
| 25.00 @ 587.6nm                                                                       |
| <b>Back Focal Length BFL (mm):</b><br>22.50                                           |
| <b>Coating:</b><br>VS 0° (425-675nm)                                                  |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤0.4% @ 425 - 675nm                 |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">N-BK7</a>                   |
| <b>Surface Quality:</b><br>40-20                                                      |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                                 |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                                           |
| <b>Focal Length Tolerance (%):</b><br>±1                                              |
| <b>Centering (arcmin):</b><br><1                                                      |
| <b>Center Thickness CT (mm):</b><br>3.80 ±0.10                                        |
| <b>Edge Thickness ET (mm):</b><br>1.40                                                |
| <b>Radius R<sub>1</sub> (mm):</b><br>12.92                                            |
| <b>Clear Aperture CA (mm):</b><br>14                                                  |
| <b>f/#:</b><br>1.67                                                                   |
| <b>Numerical Aperture NA:</b><br>0.30                                                 |
| <b>Type:</b><br>Plano-Convex Lens                                                     |
| <b>Bevel:</b><br>Protective bevel as needed                                           |
| <b>Wavelength Range (nm):</b><br>425 - 675                                            |
| <b>Damage Threshold, Reference:</b> <input type="checkbox"/><br>5 J/cm² @ 532nm, 10ns |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |