

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



12mm Focal Length



Stock #15-635 3-4 DAYS



1



€310,00

ADD TO CART

Qty 1+

€310,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:
Fixed

Horizontal Field of View, 1/2" Sensor:
30.2°

Horizontal Field of View, 2/3" Sensor:
41.0°

Filter Thread:

M30.5 x 0.50 (Female)
Horizontal Field of View, 1/3" Sensor: 22.8°
Maximum Rear Protrusion (mm): 0.6
Maximum Image Circle (mm): 11.00
Numerical Aperture NA, Object Side: 0.0059
Number of Elements (Groups): 7 (7)
Note: C-Mount compatible with O-ring 25mm ID x 2mm
Horizontal Field of View, 1/1.8" Sensor: 33.8°
Horizontal Field of View, 1/2.5" Sensor: 27.4°
Type: Fixed Focal Length Lens
Focal Length FL (mm): 12.00
Primary Magnification PMAG: 0.1X
Maximum Sensor Format: 2/3"
Working Distance (mm): 100 - ∞
Mount: C-Mount
Aperture (f/#): f/8
Coating Specification: 425 - 675nm BBAR
Entrance Pupil Position (mm): 17.6208
Horizontal Field of View, 1/4" Sensor: 17.1°
Object Space Principal Plane (mm): 23.93
Image Space Principal Plane (mm): 1.98
Field of View at Max Sensor Format: Horizontal: 41.0° Vertical: 31.3° Diagonal: 50.5°
Maximum Distortion (%): 2.11
Exit Pupil Position (mm): -11.3801
Environmental Rating: IPX7 and IPX9K
Lens Wavelength Range: VIS
Storage Temperature (°C): -20 to +60 For questions regarding operating temperature please contact our support team

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View