


1.3 OD, 25mm Dia., NIR I Coated, Absorptive ND Filter

See More by [Hoya](#)



Anti-Reflection (AR) Coated HOYA Absorptive Neutral Density (ND) Filters

Stock #13-173 3-4 DAYS

-

1

+

€73,00

ADD TO CART

Qty 1-10
€73,00
Qty 11+
€65,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm): 25.00
Optical Density OD (Average): 1.3 ±0.1 @ 400-700nm (Uncoated Filter)
Nominal Optical Density @ Center of Coating:

0.76 @ 900nm
Glass/Filter Number: Hoya ND-0.3
Substrate: ☐ ND Filter Glass
Coating: NIR I (600-1050nm)
Index of Refraction n_d: 1.51
Surface Quality: 80-50
Transformation Temperature (°C): 490
Thickness (mm): 1.45
Thickness Tolerance (mm): ±0.5
Transmission (%): 5.0 (average) @ 400 - 700nm
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 400 - 700
Dimensional Tolerance (mm): ±0.1
Parallelism (mm): <0.02
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Wavelength Range (nm): 600 - 1050
Stock No. of Uncoated Filter: #63-463

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant