

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 15mm Square Protected Silver Coated, λ/10 Mirror



15mm Square Protected Silver Coated, λ/10 Mirror, #68-326

Stock #68-326 3-4 DAYS

- 1 +

€98,00

ADD TO CART

Qty 1-5

€98,00

Qty 6+

€78,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V): λ/10 (measured before coating)

Substrate: Fused Silica (Corning 7980)

Back Surface: Commercial Polish

Surface Quality: 20-10
Dimensions (mm): 15.0 x 15.0
Dimensional Tolerance (mm): +0.0/-0.20
Coating Specification: R _{avg} >98% @450 - 2000nm R _{avg} >98% @2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%) 90
Edges: Ground
Parallelism (arcsec): 30
Thickness (mm): 3.00 ±0.20
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 10
Wavelength Range (nm): 450 - 10000
Length (mm): 15.00
Width (mm): 15.00
Damage Threshold, Reference: ☐ 0.5 J/cm ² @532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant