

TECHSPEC® 150mm Dia., 0.63 Numerical Aperture Uncoated, Aspheric Lens



Stock **#15-012** 3-4 DAYS

[Other Coating Options](#)

- 1 + **€2.100,00**

ADD TO CART

Qty 1-5
€2.100,00

Qty 6+
€1.680,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
150.00 +0.0/-0.1

Effective Focal Length EFL (mm):
120.00 @587.6nm

Numerical Aperture NA:

0.63
Back Focal Length BFL (mm): 92.86
Substrate: N-SF5
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: Uncoated
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 128
Edge Thickness ET (mm): 7.30
Center Thickness CT (mm): 45.40 ±0.1
f/#: 0.80
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 380 - 2500
Conjugate Distance: Infinite
Power (diopters): 8.33

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View