

TECHSPEC® 15mm Dia 0.75 NA, NIR Coated, UV Fused Silica Aspheric Lens



TECHSPEC UV Fused Silica Aspheric Lenses



Stock **#33-963** 3-4 DAYS

[Other Coating Options](#)

1

€490,00

ADD TO CART

Qty 1-5

€490,00

Qty 6+

€392,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
15.00 +0.0/-0.1

Effective Focal Length EFL (mm): 10.00 @ 587.6nm
Numerical Aperture NA: 0.75
Back Focal Length BFL (mm): 2.69
Substrate:  Fused Silica (Corning 7980)
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: NIR (600-1050nm)
Coating Specification: R _{avg} ≤ 1.5% @ 600 - 1050nm
Centering (arcmin): ≤ 5
Surface Quality: 60-40
Clear Aperture CA (mm): 13.5
Edge Thickness ET (mm): 3.70
Center Thickness CT (mm): 11.40 ± 0.1
f/#: 0.67
Bevel: Protective bevel as needed
Radius R₂ (mm): 19.138
Shape of Back Surface: Convex
Type: Aspheric Lens
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite
Power (diopters): 100.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant