

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

1550nm CWL, 25mm Dia., OD 4 Ultra Narrow Filter



Ultra Narrow Bandpass Filters



Stock #12-514 3-4 DAYS

1 €2.075,00

ADD TO CART

Qty 1-9

€2.075,00

Qty 10+

€1.900,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Angle of Incidence (°):

0
Optical Density OD (Average): 4.00
Clear Aperture CA (mm): 21.34
Center Wavelength CWL (nm): 1,550.60
Full Width-Half Max FWHM (nm): 2.00
Substrate:  Fused Silica (Coming 7980)
Minimum Transmission (%): >90
Coating: Hard Coated
Transmission (%): T _{abs} >90% @ 1550.6nm
Type: Bandpass Filter
Blocking Wavelength Range (nm): 900 - 1533, 1569 - 1650
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 5.00 ±0.05
Note: Filter Design: Multi-Cavity
Substrate Thickness (mm): 2.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant