

TECHSPEC® 1.5X, 532nm Vega® Nd:YAG Laser Line Beam Expander



TECHSPEC® Vega™ Laser Line Beam Expanders



Stock #12-874 3-4 DAYS

⊖ 1 ⊕

€342,00

ADD TO CART

Qty 1-9

€342,00

Qty 10+

€302,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0

Coating:

Laser V-Coat (532nm)
Design Wavelength DWL (nm): 532
Entrance Aperture (mm): 10
Exit Aperture (mm): 23
Expansion Power: 1.5X
Substrate: ☐ Fused Silica (Corning 7980)
Length (mm): 83.80
Transmission (%): >99 (nominal)
Weight (g): 75
Housing Diameter (mm): 29.95
Transmitted Wavefront, P-V: <λ/10 for 4mm input beam (nominal, λ = DWL)
Type: Beam Expander
Mounting Threads: Input: Male M30 x 1 Output: Female M27 x 0.5
Coating Specification: R _{abs} <0.25% @ 532nm
Wavelength Range (nm): 500 - 570
Style: Fixed Magnification
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns, 20Hz
Divergence Adjustment: Rotating Optics

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View