

TECHSPEC® 15mm Dia., 0.5mm Thick, Uncoated, Sapphire Window



Stock #17-225 3-4 DAYS

⊖ 1 ⊕ **€61,50**

ADD TO CART

Qty 1-24

€61,50

Qty 25+

€49,25

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number (v_d):
72.24

Axis Orientation:
Random

Bevel:
Protective as needed

Birefringence ($n_o - n_e$): 0.008 for Visible Light Orthogonal to Optical Axis
Clear Aperture (%): ≥90
Diameter (mm): 15.00 ±0.05
Thickness (mm): 0.50 ±0.05
Coating: Uncoated
Coefficient of Thermal Expansion CTE ($10^{-6}/^{\circ}\text{C}$): 8.8
Density (g/cm^3): 3.97
Edges: Fine Ground
Index of Refraction n_d: 1.77
Knoop Hardness (kg/mm^2): 1900
Parallelism (arcmin): ≤3.5
Poisson's Ratio: 0.27
Substrate: Sapphire (Al_2O_3)
Surface Flatness (P-V): 2λ (typical)
Surface Quality: 80-50
Type: Protective Window
Wavelength Range (nm): 330 - 5500
Young's Modulus (GPa): 435

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
REACH 241: Compliant